





MT-605


Tube & Digital Amplifier

Safety Instructions

- 1、Please do not sprinkle water on the machine, please do not place vases or items filled with liquid on the machine.
- 2、The tube is very hot when it working, please don't touch it.
- 3、Please do not open the machine for maintenance or modification by yourself. Opening the machine and arbitrarily modifying the internal circuit will make it difficult for maintenance personnel to repair the machine, and will affect the performance or quality of the machine.
- 4、Please place this unit in a well-ventilated place, avoid direct sunlight, and the machine should leave at least the following clearances:



Top:30CM Side:10CM



Back:10CM

Operation Notes:

1、Turn on the power

Before turning it on, please check again whether connections are correct and specifications of adapter are correct.

2、Avoid mobile phones

Please do not place your mobile phone near this unit, it may cause noise disturbance.

3、Move the machine

Please disconnect the power adapter and cables before moving the machine.

Introduction

MT-605 is a high-performance tube & digital power amplifier. The pre-stage uses tubes to making the sound soft and mellow, the rear-stage uses high-fidelity high-power digital power chips, can output up to 30W/channel, it can easily drive most bookshelf speakers or small speakers, and can ensure excellent sound. It is the best choice for your speakers on the computer desk.

Parameters

Power Supply:DC24V

Output Power: 2*30W

THD+N:0.1%@1kHz

SNR:85dB


Frequency Response:20Hz-40kHz


Size:12.0*11.4*6.7cm

Weight:0.39KG

Parts and Controls

- 1、Power switch;
- 2、Volume knob: Rotate clockwise to increase the volume, counterclockwise to decrease the volume;
- 3、Tube;
- 4、Analog signal input;
- 5、Speaker connector (right channel);
- 6、Speaker connector (left channel);
- 7、Power in, DC24V/3A; DC plug size is $\Phi 5.5 \times 2.5\text{mm}$.





Package List

MT-605	1pc
Power Adapter	1pc
AC Cable	1pc
User's Manual	1pc
Warranty Card	1pc

Maintenance Instruction

1. Do not place the unit under the hot sunshine or near the heating equipment.
2. Do not place the machine in high temperature or dusty place, or put any items with water on it.
3. Do not use chemical solvents to clean the machine, otherwise it may damage the surface coating, please use soft dry cloth to wipe it.
4. Turn the unit power off when without using for a long time.
5. Don't repair the unit by yourself, if any problems, should send it to the local dealers for repair.

Warranty Information

Our products can enjoy 12-month free warranty services from the date of the sale, if the warranty period is expired, our company will charge parts cost depend on the product fault conditions. Accessories are not covered under warranty.

xDuo Technology Co.,LTD

Address:Romm F1510,MingYueHuaDu Building,GongHe Industrial Road,
XiXiang Town,Bao' an District,ShenZhen,China

Phone:+86-0755-297799189

Post code:518000

Email:service@xduoo.com